



# MSR Gold™ FastFit

## MSR Gold™ 700/2 FastFit 1CT/8

All lamps burn out eventually, but when this happens with single ended MSR Gold™ FastFit, it is replaced in seconds – thanks to the specially designed lamp base and lamp holder. This lamp provides a high beam intensity of pure, white light for a truly illuminating performance, while the gold-plated caps provide superior heat protection and prevent premature failure. P3 technology allows use in any position and at higher temperatures, further extending lamp life and consistency of high-quality light output. Also, because the FastFit design is applied to Philips Halogen lamps, switching between lamp technologies can be done quickly and easily. The Philips MSR Gold™ FastFit can be operated in a lamp wattage range between 700W and 2500W.

### Product data

General Information		Operating and Electrical	
Cap-Base	PGJX50 [ PGJX50]	Power (Rated) (Nom)	700 W
Operating Position	UNIVERSAL [ Any or Universal (U)]	Lamp Current (Nom)	10.2 A
Main Application	Entertainment	Ignition Supply Voltage (Min)	198 V
Life To 50% Failures (Nom)	750 h		
System Description	FastFit		
Light Technical		Controls and Dimming	
Color Code	2	Dimmable	Yes
Luminous Flux (Min)	41800 lm		
Luminous Flux (Nom)	50000 lm	Mechanical and Housing	
Chromaticity Coordinate X (Nom)	298	Cap-Base Information	PGJX50
Chromaticity Coordinate Y (Nom)	322		
Correlated Color Temperature (Nom)	7500 K	Luminaire Design Requirements	
Luminous Efficacy (rated) (Nom)	71 lm/W	Bulb Temperature (Max)	950 °C
Color Rendering Index (Nom)	75	Pinch Temperature (Max)	500 °C
Product Data			
		Full product code	872790090850300

**Prodotti commercializzati da:**  
**AMLUX s.r.l.**  
**46042 Castel Goffredo (MN)**  
**info@amlux.it - www.amlux.it**

# MSR Gold™ FastFit


Order product name	MSR Gold™ 700/2 FastFit 1CT/8
EAN/UPC - Product	8727900908503
Order code	928106205114
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	8

Material Nr. (12NC)	928106205114
Net Weight (Piece)	0.100 kg

## Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


## Dimensional drawing




MSR GOLD 700/2 FastFit

Product	D (max)	O	L (min)	L (max)	L	C (max)	F
MSR Gold™ 700/2 FastFit 1CT/8	23.2 mm	3.8 mm	64 mm	66 mm	65 mm	112 mm	50 mm

## Photometric data



MSR Gold™ 700(2) FastFit



MSR Gold™ 700(2) FastFit

**Prodotti commercializzati da:**  
**AMLUX s.r.l.**  
**46042 Castel Goffredo (MN)**  
**info@amlux.it - www.amlux.it**



**Prodotti commercializzati da:**  
**AMLUX s.p.a.**  
**46042 Castel Goffredo (MN)**  
**info@amlux.it - www.amlux.it**

© 2017 Philips Lighting Holding B.V. All rights reserved. Philips Lighting reserves the right to change specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

[www.lighting.philips.com](http://www.lighting.philips.com)

2017, May 26 - data subject to change